

BrainChild

MKT Data Logger XH10 / XH11



General Description

The XH-Logger is a compact, portable device ideal for recording temperature and humidity. It provides temperature and humidity measurements suitable for various requirements and has multiple recording methods, data analysis capabilities, and report output functions. XHLogger supports two types of sensors: internal and external, which can be used in different locations for various monitoring applications.

XH10: Internal sensor, suitable for factory or warehouse monitoring.

XH11: External sensor, suitable for refrigerators, moisture-proof boxes, or any cabinet where users need to view values from the outside.

Specifications



- One-Key Start/Stop or set Start/Stop at a scheduled time.
- Set parameters, download PDF reports and supply power via the USB interface.
- Temperature and humidity statistical data.
- Provide temperature measurements in Celsius (°C) and Fahrenheit (°F).
- Temperature/humidity and device status on the LCD screen.
- Temperature and humidity data tracking.
- Configurable sampling rate.
- User-friendly software, DLV (Data Logger Viewer).
- High power efficiency.
- IP65 protection.
- Display Mean Kinetic Temperature (MKT).


Specifications

Power Supply	USB/ER14250 Battery(1 year battery life @ 1 min. log interval)
USB Voltage(@500mA)	Min.: 4.5 VDC Normal: 5 VDC Max.: 5.5 VDC
Log Interval	1 sec~24 hrs
Temp. display resolution	0.1 °C /°F
Operating range	Temp.: -10°C (14°F) ~ 60°C (122°F) Humidity: 10%RH~90%RH
Accuracy	Temp.: 0°C ~ 50°C (±0.3°C), others ±0.5°C Humidity: 20%~80%@25°C(±3%RH) others ±5%RH
Internal Memory	Maximum 100 files (record start to stop as one file), maximum 79,872 logs, maximum 200,192 logs.
Protective Class	IP65
Dimensions	65.1 x 70 x 23.25mm
Weight	82.1 g (with battery, external sensor excluded)

Outlook ▶



Mounting Plate ▶



Memory Management ▶

The total memory of the system is 200,192 records, which can be used for up to 100 files. The size of each file is maximum 79,872 records. The memory space is shown as follows.



Configuration Home ▶

Home:

Temperature

Home:

MKT



Users can set home page to display temperature, humidity, max/min temperature, or MKT.

PC Software

Data Logger Viewer (DLV) is available for download at www.brainchildtw.com. The software is easy to install and use. It is important that users configure the new XHLogger before using it.

Sensor List

ID	Name	Serial	Model	IP	Port	Status	Power	Temp	Humidity	Pressure	Light	CO2	PM2.5	PM10	SO2	NO2	CO	TVOC	Wetness	Velocity	Direction	Current Data
1	XHLogger	XXXXXXXXXX	XH-001	192.168.1.10	4444	Online	5V	25.0	65%	1013.2	0.1	0.2	1.0	2.0	0.0	0.0	0.0	0.5	100%	100%	000	100%
2	XHLogger	XXXXXXXXXX	XH-002	192.168.1.11	4444	Online	5V	25.0	65%	1013.2	0.1	0.2	1.0	2.0	0.0	0.0	0.0	0.5	100%	100%	000	100%

List all XHLoggers connected to PC and display the status.

Parameter Configuration



On Parameter page, users can configure the Name, Time Zoom, and Start/Stop mode of the XHLogger.

Tip: If multiple XHLoggers with the same configuration are required, users can use the 'Copy' and 'Paste' functions on all XHLoggers.

History Reviewing

ID	Serial	Model	IP	Port	Status	Power	Temp	Humidity	Pressure	Light	CO2	PM2.5	PM10	SO2	NO2	CO	TVOC	Wetness	Velocity	Direction	
1	XXXXXXXXXX	XH-001	192.168.1.10	4444	Online	5V	25.0	65%	1013.2	0.1	0.2	1.0	2.0	0.0	0.0	0.0	0.5	100%	100%	000	100%

Download the records to your PC and review the data.

Tip: You can press 'Ctrl' and select multiple sets of historical data, then analyze these data in the same report.

Graphic



Users can use the recorded data to generate graphics to compare with data from other XHLoggers.

Application

The XH10 and XH11 are perfect solutions for recording and monitoring temperature and humidity in warehouses, vaccine refrigerators, cold chain management, temperature mapping, greenhouse planting, museums, and art galleries.


Temperature Mapping



Cultivation of crops with high economic value



Collection of rare items



Storage of temperature sensitive materials

BrainChild

Brainchild Electronic Co., Ltd.
www.brainchildtw.com

209 Chongyang Road, Nangang Dist., Taipei, 11153, Taiwan
Tel: +886-2-2786-1299 Fax: +886-2-2786-1395
Email: sales@brainchild.com.tw